

The BA458C is an intrinsically safe secondgeneration flow batch controller that supersedes the successful BA350BP and BA350BC. This controller is ideal for accurately dispensing liquids, solids or components in a hazardous area and despite its sophisticated control functions, it is very easy to configure and use. Carefully designed display screens, annotated in English, French, or German, lead the user intuitively through the available options. The BA458C accepts a pulse or 4/20mA analogue input and incorporates a square root extractor and sixteen point lineariser allowing use with almost any flowmeter or sensor. Separate total and rate scaling factors enable the dispensed quantity and the rate of dispensing to be displayed in the same or in different engineering units.

Single or two-stage control can be performed by the BA458C with a third output available to control an additional valve or pump. To ensure maximum accuracy, overrun compensation may be selected to automatically minimise batching errors caused by actuator delays.

The backlit display is readable in all lighting conditions. The user screen may be selected so that the operator is only presented with essential process information. Variables that may be displayed include dispensed quantity, batch setpoint, rate of dispensing and controller status. Most of the standard display screens also include a bargraph showing batch progress. A record of total product dispensed is maintained as a grand total together with a history of the last ten batches.

Up to nine setpoints may be pre-entered and selected by the operator when required. To simplify selection, each setpoint may be identified by a plain language name having up to sixteen alphanumeric characters.

The three isolated outputs are individually configured as control or status outputs. If more are required, a factory fitted option provides three additional identical isolated outputs.

Front panel push buttons allow the operator to start and stop the batch and to reset the controller at the end of each cycle. For applications where large or remote push buttons are required, control may be transferred to external switches with or without inhibiting the front panel controls.

Counting may be inhibited during a batch by closing an external contact. Thus product may be re-cycled whilst being heated, or the batching system may be purged without affecting the quantity dispensed.

Selectable automatic restart causes the BA458C batch controller to execute the batching operation a pre-set number of times. The delay between batches may be set between 1 second and 24 hours, thus enabling the controller to perform regular dosing and sampling operations.

ATEX certification permits the BA458C to be installed in all hazardous gas areas. The magnetic pick-off, voltage pulse and 4/20mA inputs comply with the requirements for simple apparatus, allowing direct connection to most certified flowmeters. Switch contacts and a wide range of certified proximity detectors may also be directly connected to the BA458C. All three control outputs are galvanically isolated and certified as separate intrinsically safe circuits with output parameters complying with the requirements for simple apparatus. This allows most certified hazardous area loads such as valves, lamps, and sounders to be controlled, or the output may be transferred to the safe area via a wide range of Zener barriers or galvanic isolators.

For use in the USA and Canada the BA458C has FM and cFM intrinsic safety and nonincendive approval.

Controller configuration may be performed via the front panel push buttons or optional external switches. To prevent accidental or unauthorised adjustment, access to the configuration menus is restricted by an external security link and an optional user definable four digit security code.

For field mounting applications the BA454D provides the same batching facilities but is housed in a robust IP66 GRP enclosure suitable for external mounting. A complementary range of non-certified models for use in safe areas is also available.

BA458C Flow batch controller

Intrinsically safe for use in all gas hazardous areas

- Easy to use
- Intrinsically safe ATEX, FM & cFM certification.
- High contrast display with backlight.
- Pulse or 4/20mA current source input.
- 3 or 6 outputs
- 9 selectable batch setpoints.
- IP66 front panel
- 3 year quarantee

www.beka.co.uk/ba458c







BEKA associates Ltd. Old Charlton Rd. Hitchin, Hertfordshire, SG5 2DA, U.K. Tel. (01462) 438301 Fax (01462) 453971 e-mail sales@beka.co.uk www.beka.co.uk



SPECIFICATION

Power supply

Voltage Must be powered via a Zener barrier or

galvanic isolator, 11V min required between

terminals 1 and 2.

Current 33 mA typical when powered from 24V via

28V 300Ω Zener barrier

Pulse inputs

Linear or via 16 point lineariser

Switch contact

Closed Less than 100Ω Greater than $1k\Omega$ Open

2-wire NAMUR Proximity detector

Magnetic pick-off 40mV peak to peak min

Voltage pulse (low)

Low Less than 1V

Greater than 3V; 30V max. High

Voltage pulse (high)

Low Less than 3V

High Greater than 10V; 30V max.

Open collector

Less than $2k\Omega$ Closed Greater than $10k\Omega$ Open

Frequency

Switch contact 100Hz maximum All other pulse I/P 5kHz maximum

4/20mA input From current source Function Linear or root extracting

Voltage drop

Accuracy at 20°C Linear 0.3 % of span

Root extracting ±16 µA at input ±0.3 % of span

0.6V at 20mA

Frequency 2Hz maximum Temperature effect Less than 0.025%/°C

Linking terminals 18 & 20 prevents input Inhibit

signal being counted.

Display

Size 86.5 mm x 45 mm LCD

Backlight Green

6 selectable operator screens showing

Batch controller status combinations of:

Quantity dispensed Batch setpoint Rate of dispensing Status of control outputs

Outputs Three galvanically isolated solid state

dc switches.

Less than 50 ± 0.7 V Off Greater than $1M\Omega$

IS parameters Ui=28V; li=200mA; Pi=0.85W

Switching time 0.2s max

Control 1 Closes when start button is operated and

opens when dispensed quantity equals the

batch setpoint.

Outputs 2 & 3 may be configured as:

Control 2 or Control 3 (parameters for each

are separately adjustable)

Closes a pre-set time after Control 1 closes and open a pre-set dispensed quantity before the dispensed quantity equals the batch setpoint.

Flow alarm

Closes when the rate of dispensing falls below a pre-set value. Also causes batch controller to pause.

Reset status

Closes when controller is reset and opens

when batch is started.

Batch status

Opens when batch is started and closes

when batch is complete.

Pulse output

Scaled number of pulses proportional to quantity dispensed. Frequency 4 Hz max.

Front panel push buttons

(Control may be transferred to external switches with or without disabling the front panel push buttons.)

Start **Energises Control 1**

During a batch de-energises Control 1, 2 & 3 Stop

causing the batch to pause.

Reset Resets the batch display to zero or to the

batch setpoint if the controller is counting

down.

Menu Provides access to four functions if they are

enabled:

Select pre-entered batch setpoint Adjust batch setpoint View size of last 10 batches Configuration menu

Security

Operator menu May be protected by an optional four digit

code.

Configuration menus Protected by external link or switch, plus

optional four digit code.

Intrinsic safety **Europe ATEX**

Code Group II Category 1G Ex ia IIC T5 Ga

 $(Tamb = -40^{\circ}C \text{ to } 60^{\circ}C)$

ITS03ATEX21379X Cert. No.

Special condition only apply for installations

in Zone 0

Location Zone 0, 1 or 2

USA FM

Standard 3610 Entity

CL I; Div 1; GP A, B, C D Code

T4; Ta = 60°C

Standard 3611 Nonincendive

Code CL I; Div 2

GP A, B, C & D T4; Ta = 60°C

File 3033262

Canada cFM

3033262C File

Environmental

Operating temp -20 to 60°C (certified for use at -40°C)

Storage temp -40 to 85°C To 95% @ 40°C Humidity Front IP66, rear IP20 Enclosure

EMC In accordance with EU Directive 2004/108/

No error for 10V/m field strength between **Immunity** 150kHz and 1GHz.

Complies with the requirements for Class B **Emissions**

equipment.

Mechanical See page 148 for enclosure & terminal

details

Terminals Removable with screw clamp for 0.5 to

1.5mm² cable. 0.7 kg

Weight

Accessories

Three programmable outputs having the Additional outputs

same specification as outputs 2 & 3.

Tag number Thermally printed strip on rear of instrument.

HOW TO ORDER

Please specify


Model number **BA458C**

Please specify if required Accessories Outputs 4, 5 & 6 Additional 3 outputs


Tag strip Legend



DIMENSIONS (mm)



TERMINAL CONNECTIONS



TERMINAL DESCRIPTIONS

		DECOTIN	110110	
Case		For earthing t	he enclosure	
1 2 11 12	+ - + -	Power supply Proximity detector, switch contact or open collector A		Input Input A
13 14 15 16 17	+ + - +	High voltage Low voltage mV (Magnetic pick-off) Common for input B 4/20mA		A Input B only one inpu
18 19 20		Common for links Configure security link Inhibit input link		Externals Links
\$1 \$2 \$3 \$4 \$5 \$6 \$7		Start Stop Reset Menu Do not use Do not use Common for switches		External Switches
Case		For earthing the enclosure		
A1 A2	+	Control 1		
A3 A4	+	Output 2	Outputs 2 and 3 may each be configured to have one of six functions	
A5 A6	+	Output 3		
A7 A8	+	Output 4	If fitted optional outputs 4, 5 and 6 may each be configured to have one of six functions.	
A9 A10	+ -	Output 5		
A11 A12	+	Output 6		